



PSA PEUGEOT CITROËN use PAM-STAMP 2G for Successful Rollhemming Simulation on Vehicle Assembly Lines

PSA PEUGEOT CITROËN

THE PROCESS

Rollhemming is a sheet metal assembly process where the edge of one sheet is rolled over the edge of another to ensure a tight junction.

THE STORY

PSA Peugeot Citroën carmaker agreed to a collaboration with ESI to develop a simulation tool based on PAM-STAMP 2G for the new rollhemming process which was quickly replacing their traditional table-top hemming process. The result is a realistic simulation tool fit for field use to assist in the decision making process.

THE BENEFITS

- Truly collaborative work answering a real-life industrial need
- Process-oriented custom tool
- Provides preventive and software corrective process options


"The most significant state-of-the-art physical parameters identified by PSA's hemming specialists were integrated into PAM-STAMP 2G. Validated through real-life industrial cases, this new tool has quickly become essential to guarantee successful product definition and process reliability."

Patrice Auger
R&D Manager for Assembly Processes
PSA-Peugeot-Citroën


A NEED BORN OF PROCESS TRANSITION

When it became clear that rollhemming would soon replace traditional table-top process for the assembly of vehicle opening panels, PSA Peugeot Citroën immediately saw the need for an appropriate simulation tool. And since such a tool was not readily available on the market, it found in ESI the perfect partner to join in the challenge of developing one based on its proven PAM-STAMP 2G solution.

As the technology was recent, PSA Peugeot Citroën did not have significant experience to build on. The expected output of this 1.5-year long collaboration was to anticipate major sheet metal behavior defects including unwanted deformations and folds.



Rollhemming of a door



Complex trajectories

The simulation tool had to be able to perform complex trajectories and accommodate various roll profiles in order to render accurate material shaping. This would ultimately allow precise design of doors, hoods, back-lids, trunks and other components early in the development phase of future vehicles.

A COLLABORATION TO BUILD A CUSTOMIZED PROCESS-ORIENTED SIMULATION TOOL


To achieve this goal, PSA Peugeot Citroën shared with ESI its real industrial data and its actual industrial needs. Technical engineers at PSA also carried-out the necessary physical prototype testing to establish and fine-tune the correlation between workshop reality and digital simulation.

This collaboration based on mutual exchange and understanding led to a clearly process-oriented software solution with input parameters such as roll profile, roller angle, and trajectory, providing answers to real problems and not just numerical cases. The product effectively addresses the needs of an experienced hemming professional seeking ways to improve his process. It is truly a product tailored for an engineer designing or fine-tuning a hemming station.

INDUSTRIAL APPLICATIONS

First, rollhemming simulations were performed on the wing of a vehicle currently under development, on which the borders were closed too tightly according to product design. After reviewing the trajectory through simulation, it was decided to reshape the stamped sides and to readapt the rollhemming trajectory, which resulted in a side closing compliant to the target.

A more delicate challenge was then addressed: on the tip of the wing, a very tight radius was generating unwanted burrs and folds. **With the help of PAM-STAMP 2G, several iterations were carried out working on side height and roller trajectory to end up with an assembly closer to the target and without folds or burrs. This simulation served as basic input to set up the process, without ever requiring a physical tool.**




Straightforward user-friendly interface

"We are now able to test several product/process configurations with PAM-STAMP 2G and provide very early orientation to our technical choices. Previously, we would have had to wait to perform tests with physical tools, which would sometimes come a bit late for in-depth changes. The benefit is clearly decision aid to define more robust processes early in the design process"

Joëlle Garabed, Technical Leader of the Digital and Simulation Stamping Department, PSA Peugeot Citroën

THE PARTNERSHIP CONTINUES

As Phase 1 – the collaborative project described above – comes to an end, PSA Peugeot Citroën has trained its assembly personnel as well as upstream designers to take advantage of this new tool earlier in future vehicle developments. Other teams are also at work to integrate this simulation in the standard industrialization process. The software development achieved is available in PAM-STAMP 2G Version 2009. This leads naturally to a Phase 2 of further collaborative development with ESI to increase the solution's possibilities and reinforce post-treatment.



Wing tip simulation before and after optimizations

ABOUT ESI GROUP

ESI is a world-leading supplier and pioneer of digital simulation software for prototyping and manufacturing processes that take into account the physics of materials. ESI has developed an extensive suite of coherent, industry-oriented applications to realistically simulate a product's behavior during testing, to fine-tune manufacturing processes in accordance with desired product performance, and to evaluate the environment's impact on product performance. ESI's products represent a unique collaborative and open environment for Simulation-Based Design, enabling virtual prototypes to be improved in a continuous and collaborative manner while eliminating the need for physical prototypes during product development. The company employs over 750 high-level specialists worldwide covering more than 30 countries. ESI Group is listed in compartment C of NYSE Euronext Paris. For further information, visit www.esi-group.com.



info@esi-group.com

ESI Group
Headquarters
 100-102 Avenue de Suffren
 75015 Paris
FRANCE
 T. +33 (0)1 53 65 14 14
 F. +33 (0)1 53 65 14 12

EUROPE

BENELUX & SCANDINAVIA

ESI Group Netherlands
 Radex Innovation Centre
 room 4.57
 Rotterdamseweg 183 C
 2629 HD Delft
 The Netherlands
 T. +31 (0)15 268 2501
 F. +31 (0)15 268 2514

CZECH REPUBLIC & EASTERN EUROPE

MECAS ESI
 Brojova 2113/16
 326 00 Pilsen
 Czech Republic
 T. +420 377 432 931
 F. +420 377 432 930

FRANCE

ESI France
 Parc d'Affaires Silic
 99, rue des Solets - BP
 80112
 94513 Rungis cedex
 France
 T. +33 (0)1 49 78 28 00
 F. +33 (0)1 46 87 72 02

GERMANY

ESI GmbH
 Mergenthalerallee 15-21
 D-65760 Eschborn
 Germany
 T. +49 (0)6196 9583 0
 F. +49 (0)6196 9583 111

ITALY

ESI Italia
 Via San Donato 191
 40127 Bologna
 Italy
 T. +39 0516335577
 T. +39 0516335578
 F. +39 0516335601

SPAIN

ESI Group Hispania
 Parque Empresarial Arroyo
 de la Vega
 C/ Franca Delgado,
 11 - planta 2ª
 28108 Alcobendas (Madrid)
 Spain
 T. +34 91 484 02 56
 F. +34 91 484 02 55

SWITZERLAND

Calcom ESI
 Parc Scientifique
 EPFL / PSE-A
 1015 Lausanne-EPFL
 Switzerland
 T. +41 21 693 2918
 F. +41 21 693 4740

UNITED KINGDOM

ESI UK
 1 Robert Robinson Av.
 The Magdalen Centre
 Oxford Science Park
 Oxford OX 4 4GA
 United Kingdom
 T. +44 (0) 1865 784 830
 F. +44 (0) 1865 784 826

AMERICAS

USA

ESI North America
 32605 W 12 Mile Road
 Suite 350
 Farmington Hills, MI
 48334-3379
 USA
 T. +1 (248) 381-8040
 F. +1 (248) 381-8998

USA

ESI North America
 6767 Old Madison Pike
 Suite 600
 Huntsville, AL 35806
 USA
 T. +1 (256) 713-4700
 F. +1 (256) 713-4799

SOUTH AMERICA

ESI South America
 Av. Pedrosa de Morais,
 1619 cj.312
 São Paulo
 SP CEP 05419-001
 Brazil
 T./F. +55 (011) 3031-6221

ASIA

CHINA

ESI China
 Room 16A,
 Base F Fu Hua Mansion
 No. 8 Chaoyangmen
 North Avenue
 Beijing 100027
 China
 T. +86 (10) 6554 4907
 F. +86 (10) 6554 4911

INDIA

ESI India
 Indrakrupa #17, 100 feet
 ring road
 3rd phase, 6th block,
 Banashankari 3rd stage
 Bangalore 560 085
 India
 T. +91 98809 26926
 F. +91 80401 74705

JAPAN

ESI Japan
 5F and 16F Shinjuku Green
 Tower Bldg. 6-14-1,
 Nishi-Shinjuku
 Shinjuku-ku, Tokyo 160-0023
 Japan
 T. +81 3 6381 8490 / 8494
 F. +81 3 6381 8488 / 8489

KOREA

Hankook ESI
 157-033, 5F MISUNG
 bldg. 660-6,
 Deungchon-3Dong,
 Gangseo-ku,
 Seoul
 South Korea
 T. +82 2 3660 4500
 F. +82 2 3662 0084

SOUTH-EAST ASIA

ESI Group South-East Asia
 12, Jalan Dato Haji Harun,
 Taman Taynton, Cheras
 56000 Kuala Lumpur
 Malaysia
 T. +60 (12) 6181014